



This **B6200** series, 0.060 Two Layer Static Dissipative Lead-Free rubber mat, will not burn and is chemical resistant green in color. The green color let people know that that area is Lead-Free. Provides an excellent static safe dissipative work area. It exceeds both EOS/ESD and department of defense requirements. All mats should be used in conjunction with a common point ground system (B9702), all floor mat products should use (B9701) floor ground. **Disclaimer.** All statements of technical information are believed to be true and are based upon tests we believe to be reliable. The proper use and application for this product must be the responsibility of the user. The statements herein shall have no force or effect.



**B9703**



**INSTALLATION:**

Take out of bag  
 Take 10' common point ground B9702 and snap onto 3/8" snap on mat.  
 With other end of wire connect to ground.  
 Check with your facility people for building ground.

PROPERTIES	SPECIFICATIONS
RTT Resistance Top to Top	2.8x10 <sup>7</sup> - 6x10 <sup>8</sup> Ohms ANSI EOS/ESD S4.1RTG
Resistance to Ground	2.2x10 <sup>7</sup> - 5x10 <sup>8</sup> Ohms ANSI EOS/ESD S4.1
Charge Decay Time 5000 volts to50v	<0.01 Seconds Fed Std 101 Method 4046
Construction	Two layer rubber
Thickness	.060 +/--.010 Inches table mats
Color	Green/black
Size, Width	2',30" *3' & 4' wide 50' long
Temperature	500F-10min
Chemical Resistance	Excellent
Surface Texture	Slight
<b>Annalysis</b>	
Lead	0
Copper	0
Chlorides	0
Phosphates	0
Mercury	0
Hexavalent Chromium	0
Polbrominated Biphenyls	0
Polybrominated, diphenyl ethers	0
Halogen	0
Sodium	1.8
Silicon as si	1
SulfatSO4	<4
Nitrates	<1

TEST EQUIPMENT	
<b>B8563</b>	Analog audit kit
<b>B8571</b>	Digital & Analog audit kit
<b>BSRM-10</b>	10 light surface megohm meter
<b>BSRM-6</b>	6 light surface megohm meter
<b>B8560</b>	New megohm meter

- All Botron cut mats come with a 10' common point grounding hardware (B9702) .
- A Grounding hardware is not included with roll goods.
- Mats should be cleaned at end of each day, using a good mat cleaner. (no silicones) B8018

RELATED PRODUCTS			
<b>B6123</b>	2'X 3'	blue T2 mat w/grd	<b>B61250</b> 2'x50' blue roll
<b>B6124</b>	2'X 4'	blue T2 mat w/grd	<b>B61350</b> 3'x50' blue roll
<b>B6125</b>	2'x 5'	blue T2 mat w/grd	<b>B613050</b> 30"x40' blue roll
<b>B6126</b>	2'x6'	blue T2 mat w/grd	<b>B61450</b> 4'x50' blue roll
<b>B61304</b>	30"x4'	blue T2 mat w/grd	
<b>B6423</b>	2'X 3'	gray T2 mat w/grd	<b>B64250</b> 2'x40' gray T2 roll
<b>B6424</b>	2'X 4'	gray T2 mat w/grd	<b>B64350</b> 3'x40' gray T2 roll
<b>B6425</b>	2'X 5'	gray T2 mat w/grd	<b>B64350</b> 3'x40' gray T2 roll
<b>B64304</b>	30"x4'	gray T2 mat w/grd	<b>B643050</b> 30"x40' gray T2 roll

**BOTRON CO. INC.**

325 W. MELINDA LN  
 PHOENIX AZ 85027  
 PH# 623-582-6700  
 FAX# 623-582-6776

[www.botron.com](http://www.botron.com) [sales@botron.com](mailto:sales@botron.com)

**TWO LAYER GREEN LEAD-FREE RUBBER MATS & ROLLS**

**B6223**